



Amazing Possibilities at every turn

Bring your designs
to life with the Stratasys
J55 Prime 3D printer

Go beyond visual printing by adding tactile, functional and sensory capabilities to your in-house design process. From fast concept models to quality high-fidelity prototypes, the office-friends Stratasys® J55™ Prime 3D printers extends maximum designer output in an affordable package.



Ideas spun to life.

From perfecting products to applying concepts learned in the classroom, the J55 Prime can help you realize any number of design ideas. The J55 Prime offers a rotating print platform for outstanding surface finish and printing quality, and features multimaterial capabilities and material configurations for both industrial and mechanical design.

Designed for consistent, stable performance, the J55 Prime requires zero mechanical calibrations and features a “ready-to-print” mode, so you can turn ideas into reality without interruption.



J55 Prime

Improving Your Productivity

Productivity at your elbow. Office, classroom, or studio environment – the J55 Prime office solution is engineered to fit seamlessly into a professional space, offering design and functional flexibility.

Compact.

The J55 Prime features the best in-class footprint to printing tray ratio on the market, which means less bulk in your office and a better yield with more options.

Odor free.

Studios, offices and classrooms are not production facilities – and shouldn't need to be. The smell free system uses a ProAero Air Extractor to effectively capture and filter out fumes, for a safe and odor free operation.

Ultra-Quiet.

The J55 Prime is ultra-quiet, operating under 53 decibels – that's about the same as a household refrigerator.

Cost effective.

The Stratasys J55 Prime makes transforming your workflow a cynch while offering multimaterial prototyping - at an accessible price.

Ease of use.

Leverage an intuitive, three-step color 3D printing workflow – design, import, and print. Simply import designs using native CAD files or 3MF file formats and send models to the J55 Prime using GrabCAD Print software.

GrabCAD Printer Connectivity

Connect your PolyJet Printers into the software systems you use to manage your production process. GrabCAD Printer Connectivity integrates Stratasys PolyJet printers with enterprise applications such as ERP, BI, and Digital Rights Management. It also enables communication with MES systems to enable automation and production data collection, in addition to analytics.

Quality.

With the J55 Prime, there's no need to compromise. Upgrade your design process with high resolution, fast prints, multi-material flexible capabilities and a full color range.





Your design cycle, simplified.



Rough: Concept Models.


Reduce time spent on manual models, and iterate initial designs faster and more often. The economical DraftGrey material makes concept models easy and affordable. In the time it takes to make a single prototype using traditional methods, you can get 5x more design iterations with the Stratasys J55 Prime 3D printer.

Ready: Detailed Designs.

Incorporate color early and often. CMF designs can be introduced weeks earlier than traditional methods allow, including parts printed with several colors and textures thanks to multi-material capabilities and a simple software workflow. Parts printed on the J55 Prime require little to no post-processing, reducing labor and making your design process run smoother.

Right: High-Fidelity Prototypes.

With high-quality full-color materials and realistic surface finishing, the J55 Prime lets you create parts that look, act and feel like the real thing. Instead of wasting time and money on outsourcing, create everything in-house. Realistic prototypes let you correct mistakes and verify designs more efficiently, leading to quicker decision making and quicker approvals.



Communicate with reality.

Create prototypes that feature full color, multiple texture and truly functional realism. The J55 Prime can produce more than 640,000 distinguishable color combinations, print five resins simultaneously and provide multimaterial capabilities that bring even the most imaginative ideas to life – allowing you to make more accurate design decisions, add functionality and skin contact capabilities earlier in the process.

Power Designs With Color

Improve the speed, efficiency and color fidelity of your prototypes by 3D printing with PANTONE® colors. As a PANTONE Validated™ 3D printer, the J55 Prime enables you to match Stratasys CMYK colors to more than 1,900 printable PANTONE Colors, Solid Coated and SkinTones™.



See the specs.

Product Specifications

| | | |
|--------------------------|---|---|
| Model Materials | <input checked="" type="checkbox"/> VeroCyanV™ | <input type="checkbox"/> VeroUltra™ WhiteS |
| | <input checked="" type="checkbox"/> VeroMagentaV™ | <input checked="" type="checkbox"/> VeroUltra™ BlackS |
| | <input checked="" type="checkbox"/> VeroYellowV™ | <input type="checkbox"/> VeroUltra™ ClearS |
| | <input type="checkbox"/> VeroPureWhite™ | <input type="checkbox"/> Elastico™ Clear |
| | <input checked="" type="checkbox"/> VeroBlackPlus™ | <input checked="" type="checkbox"/> Elastico™ Black |
| | <input type="checkbox"/> VeroClear™ | <input type="checkbox"/> Vero™ ContactClear |
| | <input checked="" type="checkbox"/> DraftGrey™ | <input type="checkbox"/> Digital ABS Plus |
| | | |
| Support Materials | SUP710™ / Water Soluble Support – WSS™150 | |
| Build Size/Printing Area | Round Print Tray with up to 1,174cm ² (182 in ²) Print Height: 190mm*** (7.48 in.)*** | |
| Layer Thickness | Horizontal build layers down to 18 microns (0.0007 in.) | |
| Network Connectivity | LAN - TCP/IP | |
| System Size and Weight | 651 x 661 x 1511mm (25.63 x 26.02 x 59.49 in.); 228 kg (503 lbs.) | |
| Operating Conditions | Temperature 18 – 25 °C (64 – 77 °F); relative humidity 30-70% (non-condensing) | |
| Power Requirements | 100-240VAC, 50-60 HZ, 10A, 1 phase | |
| Regulatory Compliance | CE, FCC, EAC, cTUVus, CB, RCM | |
| Software | GrabCAD Print, SDK (API) | |
| Build Modes | High Quality Speed (HQS) – 18.75µm | |
| Accuracy | Deviation from STL dimensions, for 1 Sigma (67%) of models printed with rigid materials, based on size: under 100 mm – ±150µ; above 100 mm – ±0.15% of part length.** Deviation from STL dimensions, for 2 Sigma (95%) of models printed with rigid materials, based on size: under 100 mm – ±180µ; above 100 mm – ±0.2% of part length.** | |

** Measured when ambient temperature is 23 °C and relative humidity is 50%.

*** The maximal printable height for the J55™ Prime is 187 mm (7.36 in.).

Imagine what you could do.



Stratasys Headquarters

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

[stratasys.com](https://www.stratasys.com)

ISO 9001:2015 Certified

© 2024 Stratasys Ltd. All rights reserved. Stratasys, Stratasys signet J55, J850, GrabCAD, VeroCyanV, VeroMagentaV, VeroYellowV, VeroPureWhite, VeroPureBlack, VeroClear, VeroUltraClearS, DraftGrey, Elastico Clear, Elastico Black, Digital ABS Ivory, VeroContact Clear, SUP710, and PANTONE are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. All other trademarks belong to their respective owners. Product specifications subject to change without notice. BR_PJ_J55 Prime_0224a

