

J850™ TechStyle™

Product Specifications

Materials

- Digital Model Materials
- Unlimited number of digital materials including:**
- Over 600K available colors in both matte and glossy finishes
 - Translucent color tints
 - Flexible tactile materials in a variety of textures and colors

VeroEco™Flex family of semi-flexible materials: Clear, Black, White, Cyan, Magenta, Yellow and VeroEco™ ContactFlex. VeroEco Flex family of materials are in compliance with RSL (Restricted Substances List for Finished Products) industry standards.

	Printed Textile Testing*	100% Cotton	100% Polyester	50/50% Cotton Polyester	Linen
Industry Compliant Materials	Color fastness for washing at 40°C (1-5) ISO 105-C06:2010	5	5	5	5
	Color fastness for washing at 60°C (1-5) ISO 105-C06:2010	5	5	5	5
	Adhesion to washing at 40°C & 60°C ISO 105-C06:2010	Pass	Pass	Pass	Pass
	Color fastness to rubbing (wet 50 rubs) ISO 11640:2018	Pass	Pass	Pass	Pass
	Color fastness to rubbing (dry 150 rubs) ISO 11640:2018	Pass	Pass	Pass	Pass
	Abrasion resistance (Martindale) ISO 12947-2:2016	Pass	Pass	Pass	Pass

- Standard Materials
- VeroUltra™ & VeroVivid™ family of opaque and transparent materials + neutral shades and vibrant colors
 - Agilus30™ family of flexible materials: Clear, Black, White, Cyan, Magenta and Yellow

Support Materials SUP705™ (water jet removable) & 705B

Hardware

Build Size	<p>Fabric Size Handling: min 560 x 460mm; max 2 x 2mm</p> <p>Fabric Thickness: 0.1-3.0mm</p> <p>Interchangeable Tray for smooth production runs</p>
Effective Printing Area	460 x 360 x 50 mm (18.1 x 14.2 x 1.9 in) on a stretch of fabric up to 2m ²
Layer Thickness	Horizontal build layers down to 27-micron (0.001 in.)
Workstation Compatibility	Windows 10
Network Connectivity	LAN - TCP/IP Industry 4.0 Compliance

*Test results based on multiple textile samples comprising 3D printed elements of various colors.

J850™ TechStyle™

Product Specifications

System Size and Weight	J850 TechStyle System: 1400 x 1260 x 1100 mm (55.1 x 49.6 x 43.4 in.); 430 kg (948 lbs.)
	J850 TechStyle Material Cabinet: 1119 x 656 x 637 mm (44 x 25.8 x 25.1 in.); 153 kg (337 lbs.)
Operating Conditions	Temperature 18 – 25 °C (64 – 77 °F); relative humidity 30-70% (non-condensing)
Power Requirements	100–120 VAC, 50–60 Hz, 13.5 A, 1 phase; 220–240 VAC, 50–60 Hz, 7 A, 1 phase
Regulatory Compliance	CE, FCC, EAC, RCM, R-NZ1
Software	GrabCAD Print - GrabCAD Printer Connectivity SDK
Build Modes	High Mix: up to 7 base resins, 27-micron (0.001 in.) resolution
	High Speed: up to 3 base resins, 27-micron (0.001 in.) resolution
Accuracy	J850 TechStyle System: Typical deviation from STL dimensions, for models printed with rigid materials, based on size: under 100 mm – ±100µ; above 100 mm – ±200µ or ± 0.06% of part length, whichever is greater.
	Software: Deviation from STL dimensions, for 1 Sigma (67%) of models printed with rigid materials, based on size: under 100 mm – ±150µ; above 100 mm – ±0.15% of part length. Deviation from STL dimensions, for 2 Sigma (95%) of models printed with rigid materials, based on size: under 100 mm – ±180µ; above 100 mm – ±0.2% of part length.

USA - Headquarters

7665 Commerce Way
Eden Prairie, MN 55344, USA
+1 952 937 3000

ISRAEL - Headquarters

1 Holtzman St., Science Park
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000

stratasys.com

ISO 9001:2015 Certified

EMEA

Airport Boulevard B 120
77836 Rheinmünster, Germany
+49 7229 7772 0

South Asia

1F A3, Ninghui Plaza
No.718 Lingshi Road
Shanghai, China
Tel: +86 21 3319 6000



GET IN TOUCH.

www.stratasys.com/contact-us/locations

